

IE-FCI-HD15-FF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, VGA coupling, Signal insert VGA/ HD15, Socket / socket
Order No.	1556290000
Type	IE-FCI-HD 15-FF
GTIN (EAN)	4050118369755
Qty.	1 items

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E497345

Dimensions and weights

Net weight	9 g
------------	-----

Temperatures

Storage temperature	Operating temperature	-55 °C...105 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	14f36bdb-8bcd-4f24-8fb3-9538ad1abec6

General data

Product type	VGA coupling	Protection degree	IP20
Insert type	Signal insert VGA/HD15		

Electrical properties

Dielectric strength, contact / contact	1000 V eff / 1 min	Insulation resistance	1000 MΩ at 500 V DC
--	--------------------	-----------------------	---------------------


General standards

Certificate No. (DNV)	TAA000022B	Certificate No. (UR)	E497345
-----------------------	------------	----------------------	---------


Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-18-28-92
ECLASS 15.0	27-18-28-92		

Dimensioned drawing



Dimensioned drawing



Dimensioned drawing

