

## HSS-HF 1.6-3.2 EL Y75M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

### General ordering data

Version	TwinMark, Conductor and cable markers, 1.6 - 3.2 mm, yellow
Order No.	<a href="#">1562650000</a>
Type	HSS-HF 1.6-3.2 EL Y75M
GTIN (EAN)	4050118367539
Qty.	1 items

## HSS-HF 1.6-3.2 EL Y75M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.0303 inch
Width	5.6 mm	Width (inches)	0.2205 inch
Length	75000 mm	Length (inches)	2952.75 inch
Net weight	550 g		

## Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Type of printing	neutral	
Width	5.6 mm	
Operating temperature range, max.	105 °C	
Operating temperature range, min.	-55 °C	
Colour	yellow	
Halogen	No	
Length	75000 mm	
Basic material	Polyolefine	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Shrink sleeve reel
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>	
Number of markers per combination	1 Shrink sleeve reel = Conductor and cable markers	
Operating temperature range	-55...105 °C	
Number per roll	1	

## Conductor and cable markers

Halogen	No	Conductor cross-section, max.	1.5 mm <sup>2</sup>
Conductor cross-section, min.	0.5 mm <sup>2</sup>	Conductor O.D., max.	3.2 mm
Conductor O.D., min.	1.6 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Conductor O.D.	1.6 - 3.2 mm
Cross-section for connected wire	0.5 - 1.5 mm <sup>2</sup>		

## Important note

Product information	External roll holder 1302920000 necessary
---------------------	---

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

## HSS-HF 1.6-3.2 EL Y75M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

# Accessories

## Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

Type	RIBBON HSS HF EL 40/300...	Version
Order No.	<a href="#">1426210000</a>	Ink ribbon
GTIN (EAN)	4050118228823	
Qty.	1 ST	

## THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

Type	THM MMP EXT.RH	Version
Order No.	<a href="#">1302920000</a>	
GTIN (EAN)	4050118102307	
Qty.	1 ST	
Type	MULTIMARK ROLLER 115	Version
Order No.	<a href="#">1357420000</a>	
GTIN (EAN)	4050118160314	
Qty.	1 ST	
Type	MULTIMARK ROLLER 30	Version
Order No.	<a href="#">1357430000</a>	
GTIN (EAN)	4050118160253	
Qty.	1 ST	

## HSS-HF 1.6-3.2 EL Y75M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Accessories

[www.weidmueller.com](http://www.weidmueller.com)

### THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

Type	MULTIMARK PLUS ROLLER 1...	Version	
Order No.	<a href="#">2672590000</a>		
GTIN (EAN)	4050118708097		
Qty.	1 ST		