

CLI C 1-3 WS/SW W CD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Version	CableLine, Conductor and cable markers, 2.5 - 5 mm, 3 x 4.2 mm, white
Order No.	1568251043
Type	CLI C 1-3 WS/SW W CD
GTIN (EAN)	4032248441419
Qty.	500 items

CLI C 1-3 WS/SW W CD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	3 mm	Height (inches)	0.1181 inch
Width	4.2 mm	Width (inches)	0.1654 inch
Net weight	0.08 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Material colour according to resistance code	9	
Orientation of print	horizontal	
Type of printing	Standard	
Printing method	hot-embossing	
Version	CD	
Width	4.2 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-30 °C	
Colour	white	
Halogen	Yes	
Basic material	PVC, soft, without Cadmium	
Colour of printing	black	
Printed characters	Upper-case letters	
Number of markers per packaging unit	Form of supply	Reel
Recommended industries	Process, Machinery	
Number of markers per combination	1 Reel = Conductor and cable markers	
Operating temperature range	-30...80 °C	
Imprint	W	

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	1.5 mm ²	Conductor O.D., max.	5 mm
Conductor O.D., min.	2.5 mm	Conductor O.D.	2.5 - 5 mm
Cross-section for connected wire	1.5 - 4 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

CLI C 1-3 WS/SW W CD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Similar to illustration