

CLI M 2-4 GE/SW 2 CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 3 mm | Depth (inches) | 0.1181 inch |
| Height | 4 mm | Height (inches) | 0.1575 inch |
| Width | 11.3 mm | Width (inches) | 0.4449 inch |
| Net weight | 0.13 g | | |

Temperatures

Operating temperature range -30...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | |
|--|--------------------------------------|------|
| Material colour according to resistance code | 4 | |
| Orientation of print | horizontal | |
| Type of printing | Standard | |
| Printing method | hot-embossing | |
| Version | CD | |
| Width | 11.3 mm | |
| UL 94 flammability rating | V-0 | |
| Operating temperature range, max. | 80 °C | |
| Operating temperature range, min. | -30 °C | |
| Colour | yellow | |
| Halogen | Yes | |
| Basic material | PVC, soft, without Cadmium | |
| Colour of printing | black | |
| Printed characters | Numbers | |
| Number of markers per packaging unit | Form of supply | Reel |
| Recommended industries | Process, Machinery | |
| Number of markers per combination | 1 Reel = Conductor and cable markers | |
| Operating temperature range | -30...80 °C | |
| Imprint | 2 | |

Conductor and cable markers

| | | | |
|----------------------------------|--------------------------|-------------------------------|---------------------|
| Halogen | Yes | Conductor cross-section, max. | 500 mm ² |
| Conductor cross-section, min. | 16 mm ² | Conductor O.D., max. | 317 mm |
| Conductor O.D., min. | 10 mm | Conductor O.D. | 10 - 317 mm |
| Cross-section for connected wire | 16 - 500 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |



Similar to illustration

CLI M 2-4 GE/SW 2 CD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Holders



CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections. Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

| | | |
|------------|----------------------------|---|
| Type | CLI MH 110 HSTR | Version |
| Order No. | 0189400000 | CableLine, Accessories, 10 - 317 mm, 110 x 11.3 mm, black |
| GTIN (EAN) | 4008190144784 | |
| Qty. | 100 ST | |
| Type | CLI MH 70 HSTR | Version |
| Order No. | 0524400000 | CableLine, Accessories, 10 - 317 mm, 70 x 11.3 mm, black |
| GTIN (EAN) | 4008190075057 | |
| Qty. | 100 ST | |