BLZ/SL KO OR BX



Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image







Similar to illustration

Only connects what is supposed to be connected: the right connection at the right place.

Coding elements and locking devices clearly assign connecting elements during the manufacturing process and operation

The coding elements and locking devices are inserted prior to assembly or during the cable assembly phase. The Weidmüller alternative: configure online using the variant configurator to precode prior to delivery. Incorrect assembly on the circuit board and incorrect plugging of connecting elements is no longer possible. The advantage: no troubleshooting during manufacture and no operational errors by the user.

General ordering data

Version	PCB plug-in connector, Accessories, Coding element, orange, Number of poles: 1	
Order No.	<u>1573010000</u>	
Туре	BLZ/SL KO OR BX	
GTIN (EAN)	4008190048396	
Qty.	100 items	
Product data		
Packaging	Вох	

Catalogue status / Drawings



BLZ/SL KO OR BX



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals					
ROHS	Conform				
Dimensions and weights					
Net weight	0.69 g				
Environmental Product Comp	oliance				
RoHS Compliance Status	Compliant without exemption				
REACH SVHC	No SVHC above 0.1 wt%				
Material data					
la sulatina asstanial	DDT CF	Colour			
Insulating material Colour chart (similar)	PBT GF RAL 2000	Colour Moisture Level (MSL)	orange		
UL 94 flammability rating	V-0	Storage temperature, min.	-40 °C		
Storage temperature, max.		Operating temperature, min.	-50 °C		
	100 °C	Temperature range, installation, min.	-50 C -25 °C		
Operating temperature, max. Temperature range, installation, max.	100 C	remperature range, installation, min.	-25 C		
Rated data acc. to IEC	100 C				
nateu data acc. to IEC					
tested acc. to standard	IEC 60664-1, IEC 61984				
Packing					
Packaging	Box	VPE length	97.00 mm		
VPE width	90.00 mm	VPE height	41.00 mm		
Important note	00.00 11111	VI E Holght	41.00 mm		
IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the product can be evaluated on request.				
Notes	 Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months 				
	· ·				
Classifications	,				
	FC002943	ETIM 7 O	FC002943		
ETIM 6.0	EC002943	ETIM 7.0	EC002943		
ETIM 6.0 ETIM 8.0	EC002943	ETIM 9.0	EC002943		
ETIM 6.0 ETIM 8.0 ETIM 10.0	EC002943 EC002943	ETIM 9.0 ECLASS 9.0	EC002943 27-44-04-92		
ETIM 6.0 ETIM 8.0 ETIM 10.0 ECLASS 9.1	EC002943 EC002943 27-44-04-92	ETIM 9.0 ECLASS 9.0 ECLASS 10.0	EC002943 27-44-04-92 27-44-04-92		
Classifications ETIM 6.0 ETIM 8.0 ETIM 10.0 ECLASS 9.1 ECLASS 11.0 ECLASS 13.0	EC002943 EC002943	ETIM 9.0 ECLASS 9.0	EC002943 27-44-04-92		

Catalogue status / Drawings 2