

RSV1,6 RF4/35X7.5 SW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image


Similar to illustration

Clip on and use!

From the circuit board in the control cabinet: snap-on or mounting feet form the link between plug-in connectors and terminal rails.

Compatible with all standard sizes: TS 15 or TS 35. Combination foot or variations available.

The quick alternative to screw connections: unbeatable ease of installation and service.

The mounting foot for the terminal rails allows the universal use of pluggable connection systems on the module, the enclosure and the control cabinet and avoids patchwork solutions.

General ordering data

| | |
|--------------|---|
| Version | PCB plug-in connector, Accessories, Clip-in foot, black, Number of poles: 4 |
| Order No. | 1582910000 |
| Type | RSV1,6 RF4/35X7.5 SW |
| GTIN (EAN) | 4008 19011 1908 |
| Qty. | 10 items |
| Product data | |
| Packaging | Box |

RSV1,6 RF4/35X7.5 SW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 15.4 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

| | | | |
|---------------------------------------|----------|---------------------------------------|--------|
| Insulating material | PA 66/6 | Colour | black |
| Colour chart (similar) | RAL 9011 | Moisture Level (MSL) | |
| Contact material | Cu-alloy | Storage temperature, min. | -40 °C |
| Storage temperature, max. | 70 °C | Operating temperature, min. | -50 °C |
| Operating temperature, max. | 100 °C | Temperature range, installation, min. | -25 °C |
| Temperature range, installation, max. | 100 °C | | |

Rated data acc. to IEC

tested acc. to standard IEC 60664-1, IEC 61984

Packing

| | | | |
|-----------|----------|------------|-----------|
| Packaging | Box | VPE length | 177.00 mm |
| VPE width | 97.00 mm | VPE height | 53.00 mm |

Important note

IPC conformity Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002943 | ETIM 9.0 | EC002943 |
| ETIM 10.0 | EC002943 | ECLASS 14.0 | 27-46-04-05 |
| ECLASS 15.0 | 27-46-04-05 | | |

Example of use



Similar to illustration

