SLDF VR BK



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com







No task is too small when creating the perfect solution. Connections form just one part of the overall process. Small details are often the key to the perfect solution in applications where potentials are tested, grouped or even isolated.

A system is not a system without small but useful details:

- Test plugs ensure reliable pick-up from diagnostic sockets
- Cross-connectors ensure a stable electrical distribution contact directly at the connection
- Compartment partition elements divide a large number of male connectors into several separate socket connector channels
- Locks and clips optional vibration-resistant clip-on connection or mounting for male and female connectors In tandem with the manufacturing process and application - more accessories = smaller workload

General ordering data

Version	PCB plug-in connector, Accessories, Latches,		
	black, Number of poles: 0		
Order No.	<u>1599120000</u>		
Туре	SLDF VR BK		
GTIN (EAN)	4008190165697		
Qty.	100 items		
Product data			
Packaging	Box		

1



SLDF VR BK



Weidmüller Interface GmbH & Co. KG

27-46-04-05

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Δ				
Approvals				
ROHS	Conform			
Dimensions and weights				
Net weight	0.27 g			
Environmental Product Comp			'	
RoHS Compliance Status	Compliant without exemption			
REACH SVHC	No SVHC above 0.1 wt%			
Material data				
la culatina mantania l	DA	Calaur	blook	
Insulating material	PA 0011	Colour	black	
Colour chart (similar)	RAL 9011	Moisture Level (MSL)	40.00	
Contact material	Cu-alloy	Storage temperature, min.	-40 °C	
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C	
Operating temperature, max.	100 °C	Temperature range, installation, min.	-25 °C	
Temperature range, installation, max.	100 °C			
Rated data acc. to IEC				
tested acc. to standard	IEC 60664-1, IEC 61984	1		
	120 00004 1,120 0100-	·		
Packing				
Packaging	Box	VPE length	94.00 mm	
VPE width	91.00 mm	VPE height	16.00 mm	
Important note				
IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the production be evaluated on request.			
Notes	\bullet Long term storage of the product with average temperature of 50 $^{\circ}\text{C}$ and maximum humidity 70%, 36 months			
Classifications				
	50000046	ETIM 7.0	50000016	
ETIM 6.0	EC002943	ETIM 7.0	EC002943	
ETIM 8.0	EC002943	ETIM 9.0	EC002943	
ETIM 10.0	EC002943	ECLASS 9.0	27-44-04-92	
ECLASS 9.1	27-44-04-92	ECLASS 10.0	27-44-04-92	
ECLASS 11.0	27-46-04-05	ECLASS 12.0	27-46-04-05	

ECLASS 13.0

ECLASS 15.0

Catalogue status / Drawings 2

ECLASS 14.0

27-46-04-05

27-46-04-05