

## WO 76/25 TP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

Self-adhesive polyester labels which are suitable for A4 office laser printer.

### General ordering data

Version	WriteOn, Conductor and cable markers, 6 - 18 mm, 25.4 x 76 mm, white
Order No.	<a href="#">1609760000</a>
Type	WO 76/25 TP
GTIN (EAN)	4008 190008789
Qty.	1 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	25.4 mm	Height (inches)	1 inch
Width	76 mm	Width (inches)	2.9921 inch
Net weight	39 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Adhesive	Polyacrylate adhesive	Material colour according to resistance code	9
Number per sheet	60	Type of printing	neutral
Version	Self-adhesive	Width	76 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Colour	white
Halogen	Yes	Basic material	Vinyl film
Printed characters	without	Approval acc. to UL 969	No
Operating temperature range	-40...80 °C		

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	70 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Conductor O.D., max.	18 mm
Conductor O.D., min.	6 mm	Text field width	19.05 mm
Text field height	25.4 mm	Conductor O.D.	6 - 18 mm
Cross-section for connected wire	16 - 70 mm <sup>2</sup>		

Important note

Product information	1 BAGPACK = 60 PIECES
---------------------	-----------------------

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		