



Self-adhesive polyester labels which are suitable for A4 office laser printer.

General ordering data

Version	WriteOn, Conductor and cable markers, 8 - 32.3 mm, 25 x 127 mm, white
Order No.	1609770000
Type	WO 127/25 TP
GTIN (EAN)	4008190085810
Qty.	1 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	25 mm	Height (inches)	0.9842 inch
Width	127 mm	Width (inches)	5 inch
Net weight	33 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Adhesive	Polyacrylate adhesive	Material colour according to resistance code	9
Type of printing	neutral	Version	Self-adhesive
Width	127 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
Colour	white	Halogen	Yes
Basic material	Vinyl film	Printed characters	without
Approval acc. to UL 969	No	Operating temperature range	-40...80 °C

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	150 mm ²
Conductor cross-section, min.	70 mm ²	Conductor O.D., max.	32.3 mm
Conductor O.D., min.	8 mm	Text field width	25.4 mm
Text field height	25.4 mm	Conductor O.D.	8 - 32.3 mm
Cross-section for connected wire	70 - 150 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		