

## ZGB 30

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The ZGB 15 is a hinged group tag carrier. The tag carrier can hold the dekafix 5, WS 12/5 terminal markers or the inlay tag ESO 15.

The ZGB 30 is a hinged group tag carrier. The tag carrier can hold the dekafix 5, WS 12/5 terminal markers or the inlay tag ESO 7.

Inlay tags and protective strips can be found under "Accessories".

### General ordering data

Version	Terminal markers, Terminal marker, 32 x 7 mm, Pitch in mm (P): 5.00 Weidmueller, white
Order No.	<a href="#">1611930000</a>
Type	ZGB 30
GTIN (EAN)	4008 19000225 1
Qty.	20 items

**ZGB 30**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	10.5 mm	Depth (inches)	0.4134 inch
Height	32 mm	Height (inches)	1.2598 inch
Width	7 mm	Width (inches)	0.2756 inch
Net weight	0.48 g		

**Temperatures**

Operating temperature range -40...100 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Material colour according to resistance code	9		
Orientation of print	horizontal and vertical		
Version	Pivoting		
Width	7 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Basic material	Polyamide 66		
Number of markers per packaging unit	Form of supply	Component part	
Number of markers per combination	1 Component part = Terminal marker		
Operating temperature range	-40...100 °C		
Application/manufacturer	Weidmueller		

**Connector markers**

Pitch in mm (P) 5.00 mm

**Classifications**

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		