


CC-H 85/54 SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	ClipCard, Accessories, 90 x 58 mm, black
Order No.	1631640001
Type	CC-H 85/54 SW
GTIN (EAN)	4008 190465254
Qty.	20 items

CC-H 85/54 SW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	13 mm	Depth (inches)	0.5118 inch
Height	90 mm	Height (inches)	3.5433 inch
Width	58 mm	Width (inches)	2.2835 inch
Length	90 mm	Length (inches)	3.5433 inch
Diameter	0 mm	Net weight	21.3 g

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	-0.002 kg CO2 eq.	

General data

Material colour according to resistance code	0		
Version	Marker holder		
Width	58 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	black		
Halogen	No		
Length	90 mm		
Basic material	Polyamide 66		
Number of markers per packaging unit	Form of supply	MultiCard	
Recommended industries	Machinery		
Number of markers per combination	1 MultiCard = Accessories		
Operating temperature range	-40...100 °C		

Device markers

Diameter	0 mm	Halogen	No
----------	------	---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

CC-H 85/54 SW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Natural



- CB cable ties for the fastening of cables and markers.
- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
 - IEC 62275: 2006-conformant
 - Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

Type	CB 360/4,5 NC	Version	
Order No.	1279000000		Cable ties, 4.5 x 360 mm, Polyamide 66, 220 N
GTIN (EAN)	4008190031459		
Qty.	4000 ST		
Type	CB 365/7,5 NC	Version	
Order No.	1279100000		Cable ties, 7.5 x 365 mm, Polyamide 66, 540 N
GTIN (EAN)	4008190104665		
Qty.	1500 ST		