

ESO 5 S DIN A4 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration



General ordering data

| | |
|------------|--|
| Version | Terminal markers, Insert markers, 40 x 7 mm, white |
| Order No. | 1631920000 |
| Type | ESO 5 S DIN A4 WS |
| GTIN (EAN) | 4008190206673 |
| Qty. | 10 items |

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 1 mm | Depth (inches) | 0.0394 inch |
| Height | 40 mm | Height (inches) | 1.5748 inch |
| Width | 7 mm | Width (inches) | 0.2756 inch |
| Net weight | 10.8 g | | |

Temperatures

Operating temperature range -40...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|--|--------------------------------|-------------|--|
| Material colour according to resistance code | 9 | | |
| Orientation of print | horizontal and vertical | | |
| Number per sheet | 140 | | |
| Width | 7 mm | | |
| UL 94 flammability rating | HB | | |
| Operating temperature range, max. | 80 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | white | | |
| Basic material | Paper | | |
| Printed characters | without | | |
| Number of markers per packaging unit | Form of supply | Label sheet | |
| Number of markers per combination | 1 Label sheet = Insert markers | | |
| Operating temperature range | -40...80 °C | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000761 | ETIM 9.0 | EC000761 |
| ETIM 10.0 | EC000761 | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 | | |

Drawings

