

WTA 1/ZA WDU1.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Version	Test adapter (terminal), 1.5 mm ² , 250 V, 6 A
Order No.	1632300000
Type	WTA 1/ZA WDU1.5
GTIN (EAN)	4008190257354
Qty.	25 items

WTA 1/ZA WDU1.5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	75 mm	Depth (inches)	2.9527 inch
Height	66.1 mm	Height (inches)	2.6024 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	12.32 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	6c		
REACH SVHC	Lead 7439-92-1		
SCIP	fb1756cb-1941-42d9-9a81-7624ba3e17bb		

Material data

Basic material	PA 66	Colour	black
UL 94 flammability rating	V-2		

System specifications

Number of potentials	1	Number of levels	1
----------------------	---	------------------	---

Additional technical data

With snap-in pegs	Yes	Installation advice	Direct mounting
-------------------	-----	---------------------	-----------------

Conductors for clamping (rated connection)

Connection direction	on side	Tightening torque, max.	0.3 Nm
Tightening torque, min.	0.3 Nm	Stripping length	6 mm
Type of connection	Screw connection	Number of connections	1
Clamping range, max.	1.5 mm ²	Clamping range, min.	0.5 mm ²
Clamping screw	M 2.5	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	1.5 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm ²
Wire connection cross section, finely stranded, max.	1.5 mm ²	Wire connection cross section, finely stranded, min.	0.5 mm ²
Connection cross-section, stranded, max.	1.5 mm ²	Connection cross-section, stranded, min.	0.5 mm ²
Wire connection cross-section, solid core, max.	1.5 mm ²	Wire connection cross-section, solid core, min.	0.5 mm ²

Dimensions

Pitch in mm (P)	5.00 mm	Height with TS 35	98.2 mm
-----------------	---------	-------------------	---------

WTA 1/ZA WDU1.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

General

Number of poles	1	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

Rating data

Rated cross-section	1.5 mm ²	Rated voltage	250 V
Nominal current	6 A	Volume resistance according to IEC 60947-7-x	1.83 mΩ
Power loss in accordance with IEC 60947-7-x	0.56 W		

Classifications

ETIM 8.0	EC002555	ETIM 9.0	EC002555
ETIM 10.0	EC002555	ECLASS 14.0	27-25-03-04
ECLASS 15.0	27-25-03-04		