

ZBW-6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Z-series, Operating tool
Order No.	1650700000
Type	ZBW-6
GTIN (EAN)	4008 190299378
Qty.	1 items

ZBW-6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	23.75 mm	Depth (inches)	0.935 inch
Height	147 mm	Height (inches)	5.7874 inch
Width	27.76 mm	Width (inches)	1.0929 inch
Net weight	17.6 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-40 °C...55 °C
Continuous operating temp., min.	-40 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	POM	Colour	orange
UL 94 flammability rating	HB		

System specifications

Version	Operating tool
---------	----------------

Additional technical data

Installation advice	Direct mounting	Explosion-tested version	No
---------------------	-----------------	--------------------------	----

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 14.0	21-04-50-03
ECLASS 15.0	21-04-50-03		