

HDC 16D SLU 2PG21G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Version	HDC enclosures, Installation size: 3, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, high, without cover, Size of cable entries: PG 21
Order No.	1652840000
Type	HDC 16D SLU 2PG21G
GTIN (EAN)	4008190402914
Qty.	1 items

HDC 16D SLU 2PG21G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E92202

Dimensions and weights

Height	74 mm	Height (inches)	2.9134 inch
Width	71.7 mm	Width (inches)	2.8228 inch
Mounting dimension - height	45 mm	Mounting dimension - width	70 mm
Net weight	255.2 g		

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	e98b2b24-ba23-41bf-8d19-0dda3647412f

Chemical resistance	Substance	Acetone
	Chemical resistance	Conditionally resistant
	Substance	Drilling oil
	Chemical resistance	Resistant
	Substance	Diesel
	Chemical resistance	Resistant
	Substance	Ethyl alcohol
	Chemical resistance	Resistant
	Substance	Transmission oil
	Chemical resistance	Resistant
	Substance	Hydraulic oil
	Chemical resistance	Resistant
	Substance	Coolant
	Chemical resistance	Resistant
	Substance	Petroleum benzine
	Chemical resistance	Resistant
	Substance	Sweat
	Chemical resistance	Resistant
	Substance	Premium gasoline
	Chemical resistance	Conditionally resistant
	Substance	Water
	Chemical resistance	Resistant
	Substance	UV
	Chemical resistance	Unstable
	Substance	Ozone
	Chemical resistance	Unstable

Dimensions

Hole pitch length A2	70 mm	Cable entry	w. thread
Width housing C	43 mm	Width base C1	54.5 mm

HDC 16D SLU 2PG21G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Total length housing	60 mm	Height of housing B	74 mm
Height of base B1	5 mm		

General data

Tightening torque	1.2 Nm	Housing main material	diecast aluminium
Surface finish	Powder coating	Protection degree	IP65, in plugged condition
EMC housings	No	Material of locking element	Stainless steel, rust-proof


Version

Size of cable entries	PG 21	Top part/bottom part/lid	lower part
Tightening torque	1.2 Nm	Number of cable entry on top	0
Number of cable entry sideways	2	Design of cover	without cover
Design of housing	Base housing	Design of locking system	End-locking clamp, lower side
Design	high	Installation size	3
Cable entry	w. thread	Type	Base housing
Clamp version	End-locking clamp	Sealing	NBR
Internal thread	PG 21	Colour (RAL)	RAL 7035
BG	3	Suitable for ModuPlug®	Yes

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02
ECLASS 13.0	27-44-02-02	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

Drawings



HDC 16D SLU 2PG21G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 06B TOLU 1PG16G	Version
Order No.	1652640000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4008190402716	plugged condition, Cable entry from top, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, Standard, Size of cable entries: PG 16
Type	HDC 16D TOLU 1PG21G	Version
Order No.	1652680000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4008190402754	plugged condition, Cable entry from top, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, high, Size of cable entries: PG 21
Type	HDC 16D TOLU 1PG29G	Version
Order No.	1652700000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4008190402778	plugged condition, Cable entry from top, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, high, Size of cable entries: PG 29
Type	HDC 06B TOLU 1PG13G	Version
Order No.	1670500000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4008190431587	plugged condition, Cable entry from top, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, Standard, Size of cable entries: PG 13.5
Type	HDC 16D TOLU 1M32G	Version
Order No.	1787490000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4032248204830	plugged condition, Cable entry from top, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, high, Size of cable entries: M 32
Type	HDC 16D TOLU 1M25G	Version
Order No.	1787500000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4032248204847	plugged condition, Cable entry from top, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, high, Size of cable entries: M 25
Type	HDC 06B TOLU 1M25G	Version
Order No.	1788110000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4032248205554	plugged condition, Cable entry from top, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, Standard, Size of cable entries: M 25
Type	HDC 06B TOLU 1M20G	Version
Order No.	1788120000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4032248205561	plugged condition, Cable entry from top, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, Standard, Size of cable entries: M 20

HDC 16D SLU 2PG21G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Hood, Cable Entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 06B TSLU 1PG16G	Version
Order No.	1652520000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4008190402594	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, Standard, Size of cable entries: PG 16
Type	HDC 16D TSLU 1PG21G	Version
Order No.	1652560000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4008190402631	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, high, Size of cable entries: PG 21
Type	HDC 16D TSLU 1PG29G	Version
Order No.	1652580000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4008190402655	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, high, Size of cable entries: PG 29
Type	HDC 06B TSLU 1PG13G	Version
Order No.	1670530000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4008190431617	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, Standard, Size of cable entries: PG 13.5
Type	HDC 16D TSLU 1M32G	Version
Order No.	1787470000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4032248204816	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, high, Size of cable entries: M 32
Type	HDC 16D TSLU 1M25G	Version
Order No.	1787480000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4032248204823	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, high, Size of cable entries: M 25
Type	HDC 06B TSLU 1M25G	Version
Order No.	1788090000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4032248205530	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, Standard, Size of cable entries: M 25
Type	HDC 06B TSLU 1M20G	Version
Order No.	1788100000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4032248205547	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, Standard, Size of cable entries: M 20

HDC 16D SLU 2PG21G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Cover**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 06B DODL 2BO	Version
Order No.	1665200000	HDC enclosures, Installation size: 3, Protection degree: IP65, in
GTIN (EAN)	4008190421908	plugged condition, Cover for lower part of housing, End-locking
Qty.	1 ST	clamp, lower side, Standard