

QS 2/10/4 O.STGF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

General ordering data

Version	Cross-connector (terminal), Plugged, beige, 57 A, Number of poles: 2, Pitch in mm (P): 10.00, Insulated: Yes, Width: 20 mm
Order No.	1669280000
Type	QS 2/10/4 O.STGF
GTIN (EAN)	4008190428341
Qty.	20 items

QS 2/10/4 O.STGF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	34.5 mm	Depth (inches)	1.3583 inch
Height	12 mm	Height (inches)	0.4724 inch
Width	20 mm	Width (inches)	0.7874 inch
Net weight	5.05 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	20993c56-321a-4ec1-8646-b7d545a927f2

Material data

Basic material	PA 66	Colour	beige
----------------	-------	--------	-------

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Type of fixing	Plugged	Explosion-tested version	No
Type of mounting	Plugged		

Dimensions

Pitch in mm (P)	10.00 mm
-----------------	----------

General

Number of poles	2
-----------------	---

Rating data

Rated voltage	400 V	Nominal current	57 A
---------------	-------	-----------------	------

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		