

## CC-H 85/27 SW

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

|            |  |
|------------|--|
| Version    | Device markers, Accessories, 90 x 31 mm, black |
| Order No.  | <a href="#">1675130001</a>                     |
| Type       | CC-H 85/27 SW                                  |
| GTIN (EAN) | 4008190454210                                  |
| Qty.       | 40 items                                       |

## CC-H 85/27 SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|          |       |                 |             |
|----------|-------|-----------------|-------------|
| Depth    | 13 mm | Depth (inches)  | 0.5118 inch |
| Height   | 90 mm | Height (inches) | 3.5433 inch |
| Width    | 31 mm | Width (inches)  | 1.2205 inch |
| Length   | 90 mm | Length (inches) | 3.5433 inch |
| Diameter | 0 mm  | Net weight      | 11.48 g     |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

## Environmental Product Compliance

|                          |                             |                   |  |
|--------------------------|-----------------------------|-------------------|--|
| RoHS Compliance Status   | Compliant without exemption |                   |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                   |  |
| Product Carbon Footprint | Cradle to gate              | -0.001 kg CO2 eq. |  |

## General data

|  |                            |           |  |
|--|----------------------------|-----------|--|
| Adhesive                                     | Double-sided adhesive tape |           |  |
| Material colour according to resistance code | 0                          |           |  |
| Version                                      | Marker holder              |           |  |
| Width  | 31 mm                      |           |  |
| UL 94 flammability rating                    | V-2                        |           |  |
| Operating temperature range, max.            | 100 °C                     |           |  |
| Operating temperature range, min.            | -40 °C                     |           |  |
| Colour                                       | black                      |           |  |
| Halogen                                      | No                         |           |  |
| Length                                       | 90 mm                      |           |  |
| Basic material                               | Polyamide 66               |           |  |
| Number of markers per packaging unit         | Form of supply             | MultiCard |  |
| Recommended industries                       | Machinery                  |           |  |
| Number of markers per combination            | 1 MultiCard = Accessories  |           |  |
| Operating temperature range                  | -40...100 °C               |           |  |

## Device markers

|          |      |         |    |
|----------|------|---------|----|
| Diameter | 0 mm | Halogen | No |
|----------|------|---------|----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |