

CC-H 85/27 GR



General ordering data

Version	Device markers, Accessories, 90 x 31 mm, grey
Order No.	1675130002
Type	CC-H 85/27 GR
GTIN (EAN)	4008190454258
Qty.	40 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	13 mm	Depth (inches)	0.5118 inch
Height	90 mm	Height (inches)	3.5433 inch
Width	31 mm	Width (inches)	1.2205 inch
Length	27 mm	Length (inches)	1.063 inch
Diameter	0 mm	Net weight	11.8 g

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	-0.001 kg CO2 eq.	

General data

Adhesive	Double-sided adhesive tape		
Material colour according to resistance code	8		
Version	Marker holder		
Width	31 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	grey		
Halogen	No		
Length	27 mm		
Basic material	Polyamide 66		
Number of markers per packaging unit	Form of supply	MultiCard	
Recommended industries	Machinery		
Number of markers per combination	1 MultiCard = Accessories		
Operating temperature range	-40...100 °C		

Device markers

Diameter	0 mm	Halogen	No
----------	------	---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		