

HDC-CM-3BCM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The ConCept system features flexible and all-purpose modules. Depending on the application, you can choose from a wide variety of modules based on your requirements. The modules differ according to electrical specifications and their respective wire connection methods. Any number of combinations can be created with the ever-growing number of modules.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	1682090000
Type	HDC-CM-3BCM
GTIN (EAN)	4008 190473839
Qty.	10 items

HDC-CM-3BCM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Length	34 mm	Length (inches)	1.3386 inch
Net weight	9.68 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

ConCept Pneumatic module

UL 94 flammability rating	V-0	Colour	black
---------------------------	-----	--------	-------

Dimensions

Total length base	34 mm	Height of socket	11.4 mm
-------------------	-------	------------------	---------

General data

Number of poles	3	UL 94 flammability rating	V-0
Volume resistance	5.00 mΩ	Colour	black
Insulation resistance	1011 Ω	Type	Female
Surge voltage category	III	Pollution severity	3
Series	ConCept module	Rated voltage (DIN EN 61984)	630 V
Rated impulse voltage (DIN EN 61984)	8 kV	Rated current (DIN EN 61984)	40 A
Free from halogens	false	Low smoke acc. DIN EN 45545-2	Yes

Connection data PE

Connection type PE	Crimp connection
--------------------	------------------

Version

Wire connection cross section AWG, max.	AWG 7	Volume resistance	5.00 mΩ
Conductor cross-section, max.	10 mm ²	Conductor cross-section, min.	1.5 mm ²

Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		