

**HDC-C-M3-BM6.0AG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Version	Heavy-duty connectors, Crimp contact, CM 3, Female, Conductor cross-section, max.: 6, turned, Copper alloy
Order No.	<a href="#">1682290000</a>
Type	HDC-C-M3-BM6.0AG
GTIN (EAN)	4008 1904 7402 7
Qty.	100 items

**HDC-C-M3-BM6.0AG**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURus)	E92202

**Dimensions and weights**

Diameter	6.1 mm	Net weight	3.05 g
----------	--------	------------	--------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

**General data**

Contact diameter, male Ø	3.6 mm	Stripping length, rated connection	10 mm
Type of connection	Crimp connection	Version insert	CM 3
Volume resistance	≤1 mΩ	Conductor cross-section, max.	6 mm <sup>2</sup>
Conductor cross-section, min.	6 mm <sup>2</sup>	Surface finish	silver
Plugging cycles	≥ 500	Type	Female
Basic material	Copper alloy	Production methods	turned
Cross-section for connected wire	6 - 6 mm <sup>2</sup>	Material of contact	Copper alloy

**Classifications**

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		

## HDC-C-M3-BM6.0AG

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Drawings

[www.weidmueller.com](http://www.weidmueller.com)



Leiterquerschnitt	Abisolierlänge	
1,50 mm <sup>2</sup>	AWG 16	10 mm
2,50 mm <sup>2</sup>	AWG 14	10 mm
4,00 mm <sup>2</sup>	AWG 12	10 mm
6,00 mm <sup>2</sup>	AWG 10	10 mm
10,00 mm <sup>2</sup>	AWG 7	10 mm



**HDC-C-M3-BM6.0AG**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**Crimping tools**



Crimping tools for turned contacts

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

**General ordering data**

Type	CTIN CM 1.6/2.5	Version	
Order No.	<a href="#">9205430000</a>	Pressing tool, Crimping tool for contacts, 0.14mm <sup>2</sup> , 6mm <sup>2</sup> , 4-indent crimp	
GTIN (EAN)	4032248733446		
Qty.	1 ST		
Type	CTX CM 3.6	Version	
Order No.	<a href="#">9018480000</a>	Pressing tool, Crimping tool for contacts, 4mm <sup>2</sup> , 10mm <sup>2</sup> , W crimp	
GTIN (EAN)	4008190884581		
Qty.	1 ST		
Type	CTIN CM 3.6	Version	
Order No.	<a href="#">9205440000</a>	Crimping tool for contacts, 1.5mm <sup>2</sup> , 10mm <sup>2</sup> , 4-indent crimp	
GTIN (EAN)	4032248734146		
Qty.	1 ST		

**Contact removal tools**



Weidmüller offers a variety of crimping tools, contact removal tools, and fibre optic tools.

**General ordering data**

Type	REMOVAL TOOL CM 3	Version	
Order No.	<a href="#">1866710000</a>	Tools, Contact Removal Tool	
GTIN (EAN)	4032248437030		
Qty.	1 ST		