



Similar to illustration



PageTab are woven-fabric labels in sheet form. Except for the 8 x 20 version, all labels have a black border.

General ordering data

| | |
|------------|---|
| Version | Device markers, Device markers, 9 x 15 mm, yellow |
| Order No. | 1686160000 |
| Type | PAGETAB 15/9 |
| GTIN (EAN) | 4008190492533 |
| Qty. | 25 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 0.08 mm | Depth (inches) | 0.0031 inch |
| Height | 9 mm | Height (inches) | 0.3543 inch |
| Width | 15 mm | Width (inches) | 0.5906 inch |
| Net weight | 10 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -29...93 °C |
|-----------------------------|-------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|--|---|-------------|--|
| Adhesive | Permanent acrylic copolymer | | |
| Material colour according to resistance code | 4 | | |
| Number per sheet | 310 | | |
| Version | Self-adhesive | | |
| Width | 15 mm | | |
| Operating temperature range, max. | 93 °C | | |
| Operating temperature range, min. | -29 °C | | |
| Colour | yellow | | |
| Basic material | Acrylic-coated fibre webbing | | |
| Printed characters | without | | |
| Number of markers per packaging unit | 7750 | | |
| Number of markers per packaging unit | Form of supply | Label sheet | |
| | Number of combinations per packaging unit | 25 | |
| | Number of markers per combination | 310 | |
| Number of markers per combination | 1 Label sheet = 310 Device markers | | |
| Operating temperature range | -29...93 °C | | |
| Imprint | Neutral | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

Drawings

