

SKMU PG7-MS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU MS (brass locknut), Locknut, PG 7, 2.8 mm, Brass, nickel-plated
Order No.	1694070000
Type	SKMU PG7-MS
GTIN (EAN)	4008190872236
Qty.	100 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	2.8 mm	Height (inches)	0.1102 inch
Net weight	1.4 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

General information

O.D.	17.33 mm	Pitch of thread	1.27 mm
Halogen	No	AF size 1	15 mm
Thickness	2.80 mm	Cable gland	PG 7
Basic material	Brass, nickel-plated	External thread	PG 7
Internal thread	PG 7	Length of thread	2.8 mm

Classifications

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

