

**SKMU PG11-MS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	SKMU MS (brass locknut), Locknut, PG 11, 3 mm, Brass, nickel-plated
Order No.	<a href="#">1694090000</a>
Type	SKMU PG11-MS
GTIN (EAN)	4008190872250
Qty.	100 items

## SKMU PG11-MS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Height	3 mm	Height (inches)	0.1181 inch
Net weight	2.3 g		

### Temperatures

Operating temperature	
-----------------------	--

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

### General information

O.D.	24.26 mm	Pitch of thread	1.41 mm
Halogen	No	AF size 1	21 mm
Thickness	3.00 mm	Cable gland	PG 11
Basic material	Brass, nickel-plated	External thread	PG 11
Internal thread	PG 11	Length of thread	3 mm

### Classifications

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

**Drawings**

