


LM WO 23/55 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Self-adhesive polyester labels which are suitable for A4 office laser printer.

General ordering data

Version	LaserMark, Conductor and cable markers, 6.8 - 12 mm, 23 x 55 mm, yellow
Order No.	1695721687
Type	LM WO 23/55 GE
GTIN (EAN)	4008 1909 2468 3
Qty.	10 items

LM WO 23/55 GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	23 mm	Height (inches)	0.9055 inch
Width	55 mm	Width (inches)	2.1654 inch
Net weight	10 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Adhesive	Acrylate	
Material colour according to resistance code	4	
Number per sheet	40	
Type of printing	neutral	
Version	Self-adhesive	
Width	55 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	150 °C	
Operating temperature range, min.	-40 °C	
Colour	yellow	
Halogen	No	
Basic material	Polyester film	
Printed characters	without	
Number of markers per packaging unit	400	
Number of markers per packaging unit	Form of supply	Label sheet
	Number of combinations per packaging unit	10
	Number of markers per combination	40
Size of labelling field	23 x 12.7 mm	
Number of markers per combination	1 Label sheet = 40 Conductor and cable markers	
Operating temperature range	-40...150 °C	

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	50 mm ²
Conductor cross-section, min.	10 mm ²	Conductor O.D., max.	12 mm
Conductor O.D., min.	6.8 mm	Text field width	22.8 mm
Text field height	12.5 mm	Conductor O.D.	6.8 - 12 mm
Cross-section for connected wire	10 - 50 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings

