

**SKMU PG9-K GR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	SKMU PA (plastic locknut), Locknut, PG 9, 5 mm, Polyamid 6 (PA6 - GF30)
Order No.	<a href="#">1697450000</a>
Type	SKMU PG9-K GR
GTIN (EAN)	4008190880569
Qty.	100 items

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Height	5 mm	Height (inches)	0.1968 inch
Net weight	1.4 g		

**Temperatures**

Operating temperature -40 °C...100 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General information**

Silicone	No	O.D.	25.41 mm
UL 94 flammability rating	HB	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.41 mm
Halogen	No	AF size 1	22 mm
Thickness	5.00 mm	Cable gland	PG 9
Basic material	Polyamid 6 (PA6 - GF30)	External thread	PG 9
Internal thread	PG 9	Length of thread	5 mm

**Classifications**

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		

**SKMU PG9-K GR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

