



Fastening of cables or bundles with ties into electrical switchgears and cabinets.

### General ordering data

|            |                                       |
|------------|---------------------------------------|
| Version    | Cable ties, 19 x 19 mm, Plastic, 80 N |
| Order No.  | <a href="#">1697950000</a>            |
| Type       | CBH 19/19 BK                          |
| GTIN (EAN) | 4008 190883027                        |
| Qty.       | 7500 items                            |

**CBH 19/19 BK**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |       |                 |             |
|------------|-------|-----------------|-------------|
| Depth      | 2 mm  | Depth (inches)  | 0.0787 inch |
| Height     | 19 mm | Height (inches) | 0.748 inch  |
| Width      | 19 mm | Width (inches)  | 0.748 inch  |
| Length     | 2 mm  | Length (inches) | 0.0787 inch |
| Net weight | 0.7 g |                 |             |

**Temperatures**

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -40...60 °C |
|-----------------------------|-------------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Installation materials**

|                                   |         |                                   |               |
|-----------------------------------|---------|-----------------------------------|---------------|
| Max. cable tie width              | 3.6 mm  | UV-resistant                      | Yes           |
| For re-opening                    | No      | Version                           | Self-adhesive |
| UL 94 flammability rating         | V-2     | Operating temperature range, max. | 60 °C         |
| Operating temperature range, min. | -40 °C  | Halogen                           | No            |
| Basic material                    | Plastic | Tensile strength                  | 80 N          |
| Tensile strength (Pound-force)    | 18 lbf  | Diameter of fastening hole        | 4.1 mm        |

**Important note**

|                     |  |
|---------------------|--|
| Product information | Number of bags in box (pieces): 75<br>Number of items in bag (pieces): 100<br>One delivery unit corresponds to one box quantity, and only multiples of the delivery unit can be ordered. |
|---------------------|--|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000449    | ETIM 9.0    | EC000449    |
| ETIM 10.0   | EC000449    | ECLASS 14.0 | 23-15-25-22 |
| ECLASS 15.0 | 23-15-25-22 |             |             |

**Drawings**

**Dimensioned drawing**

