



Fastening of cables or bundles with ties into electrical switchgears and cabinets.

General ordering data

Version	Cable ties, 19 x 19 mm, Plastic, 80 N
Order No.	1697950000
Type	CBH 19/19 BK
GTIN (EAN)	4008 190883027
Qty.	7500 items

CBH 19/19 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	2 mm	Depth (inches)	0.0787 inch
Height	19 mm	Height (inches)	0.748 inch
Width	19 mm	Width (inches)	0.748 inch
Length	2 mm	Length (inches)	0.0787 inch
Net weight	0.7 g		

Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Installation materials

Max. cable tie width	3.6 mm	UV-resistant	Yes
For re-opening	No	Version	Self-adhesive
UL 94 flammability rating	V-2	Operating temperature range, max.	60 °C
Operating temperature range, min.	-40 °C	Halogen	No
Basic material	Plastic	Tensile strength	80 N
Tensile strength (Pound-force)	18 lbf	Diameter of fastening hole	4.1 mm

Important note

Product information	<p>Number of bags in box (pieces): 75</p> <p>Number of items in bag (pieces): 100</p> <p>One delivery unit corresponds to one box quantity, and only multiples of the delivery unit can be ordered.</p>
---------------------	---

Classifications

ETIM 8.0	EC000449	ETIM 9.0	EC000449
ETIM 10.0	EC000449	ECLASS 14.0	23-15-25-22
ECLASS 15.0	23-15-25-22		

Drawings

Dimensioned drawing

