


STGH ZRV1.5/PE GN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

General ordering data

Version	Z-series, Plug housing, Rated cross-section: 1.5 mm ² , Direct mounting
Order No.	1698201001
Type	STGH ZRV1.5/PE GN
GTIN (EAN)	4008 19089 1442
Qty.	50 items

STGH ZRV1.5/PE GN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	23 mm	Height (inches)	0.9055 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	1.06 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...75 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	green
UL 94 flammability rating	V-0		

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Conductors for clamping (rated connection)

Number of connections	4
-----------------------	---

Dimensions

TS 32 offset	34.5 mm	TS 35 offset	34.5 mm
--------------	---------	--------------	---------

General

Number of poles	1	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

Rating data

Rated cross-section	1.5 mm ²
---------------------	---------------------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		