

**SKMU PG36-K GR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	SKMU PA (plastic locknut), Locknut, PG 36, 8 mm, Polyamid 6 (PA6 - GF30)
Order No.	<a href="#">1698240000</a>
Type	SKMU PG36-K GR
GTIN (EAN)	4008190884772
Qty.	25 items

## SKMU PG36-K GR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Height	8 mm	Height (inches)	0.315 inch
Net weight	10.84 g		

### Temperatures

Operating temperature -40 °C...100 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General information

Silicone	No	O.D.	69.3 mm
UL 94 flammability rating	HB	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.59 mm
Halogen	No	AF size 1	60 mm
Thickness	8.00 mm	Cable gland	PG 36
Basic material	Polyamid 6 (PA6 - GF30)	External thread	PG 36
Internal thread	PG 36	Length of thread	8 mm

### Classifications

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		

**SKMU PG36-K GR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

