

## SCT 4.6/127 C

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Weidmüller stainless steel Series contains a comprehensive assortment of stainless steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- stainless steel AISI 316,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

## General ordering data

Version	Cable ties, 4.6 x 127 mm, Stainless steel 1.4301, 445 N
Order No.	<a href="#">1699800000</a>
Type	SCT 4.6/127 C
GTIN (EAN)	4008 19089224 1
Qty.	100 items
Delivery status	This article will no longer be available in the future.
Available until	2022-10-31T00:00:00+01:00
Alternative product	<a href="#">SCT 4.6/125</a>

## SCT 4.6/127 C

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Depth	0.25 mm	Depth (inches)	0.0098 inch
Height	127 mm	Height (inches)	5 inch
Width	4.6 mm	Width (inches)	0.1811 inch
Net weight	1.6 g		

## Temperatures

Operating temperature range -80...538 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

## Installation materials

UV-resistant	Yes	For re-opening	No
UL 94 flammability rating	None	Operating temperature range, max.	538 °C
Operating temperature range, min.	-80 °C	Halogen	No
Cable diameter, max.	25 mm	Basic material	Stainless steel 1.4301
Tensile strength	445 N	Bundle diameter, max.	25 mm
Tensile strength (Pound-force)	100 lbf		

## Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

**Drawings**

**Drawing**

