



Similar to illustration

Weidmüller stainless steel Series contains a comprehensive assortment of stainless steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- stainless steel AISI 316,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

General ordering data

Version	Cable ties, 4.6 x 201 mm, Stainless steel 1.4301, 445 N
Order No.	1699810000
Type	SCT 4.6/201 C
GTIN (EAN)	4008 190892258
Qty.	100 items
Delivery status	This article will no longer be available in the future.
Available until	2022-10-31T00:00:00+01:00
Alternative product	SCT 4.6/200

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	0.25 mm	Depth (inches)	0.0098 inch
Height	201 mm	Height (inches)	7.9134 inch
Width	4.6 mm	Width (inches)	0.1811 inch
Net weight	2.2 g		

Temperatures

Operating temperature range -80...538 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Installation materials

UV-resistant	Yes	For re-opening	No
UL 94 flammability rating	None	Operating temperature range, max.	538 °C
Operating temperature range, min.	-80 °C	Halogen	No
Cable diameter, max.	51 mm	Basic material	Stainless steel 1.4301
Tensile strength	445 N	Bundle diameter, max.	50 mm
Tensile strength (Pound-force)	100 lbf		

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

Drawings

Drawing

