


MARKO-C.100X100X100 B/DR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Device markers, Device markers, 100 x 100 mm, yellow
Order No.	1700550001
Type	MARKO-C.100X100X100 B/DR
GTIN (EAN)	4008190896218
Qty.	10 items

MARKO-C.100X100X100 B/DR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.05 mm	Depth (inches)	0.002 inch
Height	100 mm	Height (inches)	3.937 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	5.8 g		

Temperatures

Operating temperature range -29...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Permanent acrylic copolymer		
Material colour according to resistance code	4		
Version	Self-adhesive		
Width	100 mm		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-29 °C		
Colour	yellow		
Basic material	Acrylic-coated fibre webbing		
Colour of printing	black		
Printed characters	Symbols		
Number of markers per packaging unit	30		
Number of markers per packaging unit	Form of supply	Label sheet	
	Number of combinations per packaging unit	10	
	Number of markers per combination	3	
Number of markers per combination	1 Label sheet = 3 Device markers		
Operating temperature range	-29...80 °C		
Imprint	Lightning flash in triangle		

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

