

DFFC .5-1.0 ZRV1.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Crimp contact (terminal), 1.5 mm ²
Order No.	1705320000
Type	DFFC .5-1.0 ZRV1.5
GTIN (EAN)	4008 190948566
Qty.	500 items

DFFC .5-1.0 ZRV1.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 0.22 g

Temperatures

Ambient temperature -5 °C...40 °C Operating temperature 130 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material Plastic Surface finish tinned
 Colour silver

System specifications

Version for holding 0.5 ... 1.0 mm²

Additional technical data

Installation advice Direct mounting

Conductors for clamping (rated connection)

Stripping length 6 mm Type of connection Crimp contact
 Wire connection cross-section, finely 1 mm² Wire connection cross section, finely 1 mm²
 stranded with wire-end ferrules DIN 46228/1, max. stranded, max.

General

Installation advice Direct mounting Surface finish tinned

Rating data

Rated cross-section 1.5 mm² Volume resistance according to IEC 1.83 mΩ
 60947-7-x
 Power loss in accordance with IEC 0.56 W
 60947-7-x

Classifications

ETIM 8.0 EC000796 ETIM 9.0 EC000796
 ETIM 10.0 EC000796 ECLASS 14.0 27-44-02-04
 ECLASS 15.0 27-44-02-04