

WSM 10 /

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

WSM small plates

- Completely rust-free and acid-resistant
- Embossed characters are still legible when painted
- Also available with custom printing, embossed on a carrier
- Contents of the WSM Service Box, 40 each of: 0-9, A-Ö, +, -, x, /, :, ,, ~, =, ü, Earth, Neutral. 200 steel cable ties (200 mm). 30 stainless steel carriers, 48 mm and 60 mm; 20 steel carriers, 84 mm, and 10 steel carriers, 108 mm and 288 mm

General ordering data

Version	Stainless steel markers, Conductor and cable markers, 5.5 x 9.9 mm, silver
Order No.	1712501739
Type	WSM 10 /
GTIN (EAN)	4008190947552
Qty.	200 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.3 mm	Depth (inches)	0.0118 inch
Height	5.5 mm	Height (inches)	0.2165 inch
Width	9.9 mm	Width (inches)	0.3898 inch
Net weight	0.13 g		

Temperatures

Operating temperature range	500 °C
-----------------------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Orientation of print	horizontal		
Type of printing	Standard		
Width	9.9 mm		
Operating temperature range, max.	500 °C		
Colour	silver		
Halogen	No		
Basic material	Stainless steel 1.4404		
Printed characters	Symbols		
Number of markers per packaging unit	Form of supply	Component part	
Number of markers per combination	1 Component part = Conductor and cable markers		
Operating temperature range	500 °C		
Imprint	/		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	500 mm ²
Conductor cross-section, min.	16 mm ²	Cross-section for connected wire	16 - 500 mm ²

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Accessories

Stainless steel



Weidmüller stainless steel Series contains a comprehensive assortment of stainless steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- stainless steel AISI 316,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

General ordering data

Type	SCT 4.6/838	Version
Order No.	1699940000	Cable ties, 4.6 x 838 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892388	
Qty.	100 ST	
Type	SCT 4.6/679	Version
Order No.	1699930000	Cable ties, 4.6 x 679 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892371	
Qty.	100 ST	
Type	SCT 4.6/520	Version
Order No.	1699920000	Cable ties, 4.6 x 520 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892364	
Qty.	100 ST	
Type	SCT 4.6/360 C	Version
Order No.	1699910000	Cable ties, 4.6 x 360 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892357	
Qty.	100 ST	
Type	SCT 4.6/266 C	Version
Order No.	1699900000	Cable ties, 4.6 x 266 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892340	
Qty.	100 ST	
Type	SCT 4.6/201 C	Version
Order No.	1699810000	Cable ties, 4.6 x 201 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892258	
Qty.	100 ST	
Type	SCT 4.6/127 C	Version
Order No.	1699800000	Cable ties, 4.6 x 127 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892241	
Qty.	100 ST	

WSM 10 /

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Holder



WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

Advantages:

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

General ordering data

Type	WSMH 84MM	Version
Order No.	1774520000	Stainless steel markers, Conductor and cable markers, 14 - 79 mm,
GTIN (EAN)	4032248 149315	84 x 11 mm, silver
Qty.	50 ST	
Type	WSMH 60MM	Version
Order No.	1774510000	Stainless steel markers, Conductor and cable markers, 14 - 79 mm,
GTIN (EAN)	4032248 149308	60 x 11 mm, silver
Qty.	50 ST	
Type	WSMH 48MM	Version
Order No.	1774500000	Stainless steel markers, Conductor and cable markers, 14 - 79 mm,
GTIN (EAN)	4032248 149292	48 x 11 mm, silver
Qty.	50 ST	
Type	WSMH 288MM	Version
Order No.	1774490000	Stainless steel markers, Conductor and cable markers, 14 - 79 mm,
GTIN (EAN)	4032248 149285	288 x 11 mm, silver
Qty.	50 ST	
Type	WSMH 108MM	Version
Order No.	1774530000	Stainless steel markers, Conductor and cable markers, 14 - 79 mm,
GTIN (EAN)	4032248 149322	108 x 11 mm, silver
Qty.	50 ST	

Cable tie tools



WSM 10 /

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

General ordering data

Type	WSM TOOL AUTOMATIK	Version	
Order No.	1774470000	Stainless steel markers, Conductor and cable markers, 180 x 275	
GTIN (EAN)	4032248149261	mm, silver	
Qty.	1 ST		
Type	WSM TOOL MANUELL	Version	
Order No.	1774480000	Stainless steel markers, Conductor and cable markers, 210 x 220	
GTIN (EAN)	4032248149278	mm, silver	
Qty.	1 ST		