

**WSH 3/H/N**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

**General ordering data**

Version	Accessories, Rail support, Wemid
Order No.	<a href="#">1715970000</a>
Type	WSH 3/H/N
GTIN (EAN)	4008190353100
Qty.	10 items

## WSH 3/H/N

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	70 mm	Depth (inches)	2.7559 inch
Height	173 mm	Height (inches)	6.811 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	22.1 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

## System specifications

Version	For the mounting rails	Mounting rail	TS 35
---------	------------------------	---------------	-------

## Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	Snap-on

## Dimensions

Pitch in mm (P)	8.00 mm	Mounting offset	68 mm
-----------------	---------	-----------------	-------

## General

Number of poles	1	Installation advice	Direct mounting
Mounting rail	TS 35		

## Classifications

ETIM 8.0	EC001166	ETIM 9.0	EC001166
ETIM 10.0	EC001166	ECLASS 14.0	27-40-06-07
ECLASS 15.0	27-40-06-07		