


SM-H 27/12.5 SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	SwitchMark, Accessories, 42 x 27 mm, black
Order No.	1716640000
Type	SM-H 27/12.5 SW
GTIN (EAN)	4008190343200
Qty.	25 items

SM-H 27/12.5 SW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	3.3 mm	Depth (inches)	0.1299 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	27 mm	Width (inches)	1.063 inch
Diameter	22 mm	Net weight	0.89 g

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.011 kg CO2 eq.	

General data

Material colour according to resistance code	0			
Version	Marker holder			
Width	27 mm			
UL 94 flammability rating	V-2			
Operating temperature range, max.	100 °C			
Operating temperature range, min.	-40 °C			
Colour	black			
Halogen	No			
Basic material	Polyamide 66			
Number of markers per packaging unit	Form of supply	MultiCard		
Number of markers per combination	1 MultiCard = Accessories			
Operating temperature range	-40... 100 °C			

Device markers

Diameter	22 mm	Halogen	No
----------	-------	---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings

