

SKMU EMV PG29**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU MS EMV (brass locknut - EMC), Locknut, PG 29, 5.7 mm, Brass, nickel-plated
Order No.	1718960000
Type	SKMU EMV PG29
GTIN (EAN)	4008190352189
Qty.	15 items
Delivery status	Discontinued
Available until	2024-08-31T00:00:00+02:00

SKMU EMV PG29

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	5.7 mm	Height (inches)	0.2244 inch
Net weight	15.73 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

General information

O.D.	47.36 mm	Pitch of thread	1.59 mm
Halogen	No	AF size 1	41 mm
Cable gland	PG 29	Basic material	Brass, nickel-plated
External thread	PG 29	Internal thread	PG 29
Length of thread	5.7 mm		

Classifications

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 9.0	27-14-44-24
ECLASS 9.1	27-14-44-24	ECLASS 10.0	27-14-44-24
ECLASS 11.0	27-14-44-24	ECLASS 12.0	27-14-08-05
ECLASS 13.0	27-14-08-05	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

