

**SKMU PG21-K SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

|                     |                                                                          |
|---------------------|--------------------------------------------------------------------------|
| Version             | SKMU PA (plastic locknut), Locknut, PG 21, 7 mm, Polyamid 6 (PA6 - GF30) |
| Order No.           | <a href="#">1719150000</a>                                               |
| Type                | SKMU PG21-K SW                                                           |
| GTIN (EAN)          | 4008190352370                                                            |
| Qty.                | 100 items                                                                |
| Delivery status     | Discontinued                                                             |
| Available until     | 2024-08-31T00:00:00+02:00                                                |
| Alternative product | <a href="#">SKMU PG21-K GR</a>                                           |

## SKMU PG21-K SW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 7 mm   | Height (inches) | 0.2756 inch |
| Net weight | 0.99 g |                 |             |

## Temperatures

Operating temperature -40 °C...100 °C

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## General information

|                                   |                         |                                   |          |
|-----------------------------------|-------------------------|-----------------------------------|----------|
| Silicone                          | No                      | O.D.                              | 41.58 mm |
| UL 94 flammability rating         | HB                      | Operating temperature range, max. | 100 °C   |
| Operating temperature range, min. | -40 °C                  | Pitch of thread                   | 1.59 mm  |
| Halogen                           | No                      | AF size 1                         | 36 mm    |
| Thickness                         | 7.00 mm                 | Cable gland                       | PG 21    |
| Basic material                    | Polyamid 6 (PA6 - GF30) | External thread                   | PG 21    |
| Internal thread                   | PG 21                   | Length of thread                  | 7 mm     |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000940    | ETIM 9.0    | EC000940    |
| ETIM 10.0   | EC000940    | ECLASS 14.0 | 27-14-08-07 |
| ECLASS 15.0 | 27-14-08-07 |             |             |

**Drawings**

