

SKMU PG29-MS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|------------|---|
| Version | SKMU MS (brass locknut), Locknut, PG 29, 4 mm, Brass, nickel-plated |
| Order No. | 1719210000 |
| Type | SKMU PG29-MS |
| GTIN (EAN) | 4008190352431 |
| Qty. | 50 items |

SKMU PG29-MS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Height | 4 mm | Height (inches) | 0.1575 inch |
| Net weight | 11.7 g | | |

Temperatures

Operating temperature

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | f350dea6-3de1-42c5-a935-c4eb3e9d5e3c |

General information

| | | | |
|-----------------|----------------------|------------------|---------|
| O.D. | 47.36 mm | Pitch of thread | 1.59 mm |
| Halogen | No | AF size 1 | 41 mm |
| Thickness | 4.00 mm | Cable gland | PG 29 |
| Basic material | Brass, nickel-plated | External thread | PG 29 |
| Internal thread | PG 29 | Length of thread | 4 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000940 | ETIM 9.0 | EC000940 |
| ETIM 10.0 | EC000940 | ECLASS 14.0 | 27-14-08-05 |
| ECLASS 15.0 | 27-14-08-05 | | |

SKMU PG29-MS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

