

**SKMU PG42-MS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	SKMU MS (brass locknut), Locknut, PG 42, 5 mm, Brass, nickel-plated
Order No.	<a href="#">1719230000</a>
Type	SKMU PG42-MS
GTIN (EAN)	4008190352486
Qty.	25 items

**SKMU PG42-MS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Height	5 mm	Height (inches)	0.1968 inch
Net weight	32.42 g		

**Temperatures**

Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

**General information**

O.D.	66.99 mm	Pitch of thread	1.59 mm
Halogen	No	AF size 1	60 mm
Thickness	5.00 mm	Cable gland	PG 42
Basic material	Brass, nickel-plated	External thread	PG 42
Internal thread	PG 42	Length of thread	5 mm

**Classifications**

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

**Drawings**

