

SKMU PG48-MS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU MS (brass locknut), Locknut, PG 48, 5.5 mm, Brass, nickel-plated
Order No.	1719240000
Type	SKMU PG48-MS
GTIN (EAN)	4008190352493
Qty.	10 items

SKMU PG48-MS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	5.5 mm	Height (inches)	0.2165 inch
Net weight	32.2 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

General information

O.D.	73.92 mm	Pitch of thread	1.59 mm
Halogen	No	AF size 1	64 mm
Thickness	5.50 mm	Cable gland	PG 48
Basic material	Brass, nickel-plated	External thread	PG 48
Internal thread	PG 48	Length of thread	5.5 mm

Classifications

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

