

**VP 7-K54****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	VPK (blanking plug in plastic), Blanking plug, in closed state, PG 7, 6 mm, IP65, Polyamid 6 (PA6 - GF30)
Order No.	<a href="#">1719250000</a>
Type	VP 7-K54
GTIN (EAN)	4008 190352509
Qty.	100 items

**VP 7-K54**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Height	2 mm	Height (inches)	0.0787 inch
Length	8 mm	Length (inches)	0.315 inch
Diameter	12.5 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	5 mm	Net weight	0.39 g

**Temperatures**

Operating temperature -40 °C...100 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General information**

Head diameter	15.00 mm	Protection degree with GWDR	IP65
UL 94 flammability rating	V-2	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Halogen	No
Protection degree	IP54	Cable gland	PG
Basic material	Polyamid 6 (PA6 - GF30)	Diameter of sealing ring	12.50 mm
External thread	PG 7	Length of thread	6 mm

**Classifications**

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

