

GWDR PG11-PO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 11, Polyethylene
Order No.	1719460000
Type	GWDR PG11-PO
GTIN (EAN)	4008190352714
Qty.	100 items

GWDR PG11-PO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	2 mm	Height (inches)	0.0787 inch
Net weight	0.15 g		

Temperatures

Operating temperature	-30 °C...90 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Silicone	Yes	Number of wires	1
O.D.	22.5 mm	Operating temperature range, max.	90 °C
Operating temperature range, min.	-30 °C	Thickness	2.00 mm
Cable gland	PG 11	Basic material	Polyethylene
Diameter of sealing ring	22.50 mm	Sealing	PE-HD
External thread	PG 11	Internal thread	PG 11
Inside diameter D2	18.60 mm		

Classifications

ETIM 8.0	EC001181	ETIM 9.0	EC001181
ETIM 10.0	EC001181	ECLASS 14.0	27-43-03-19
ECLASS 15.0	27-43-03-19		

GWDR PG11-PO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

