

GWDR PG21-PO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|------------|---|
| Version | GWDR PO (flat gasket - polyethylene), Sealing ring, PG 21, Polyethylene |
| Order No. | 1719490000 |
| Type | GWDR PG21-PO |
| GTIN (EAN) | 4008190352752 |
| Qty. | 100 items |

GWDR PG21-PO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Height | 3 mm | Height (inches) | 0.1181 inch |
| Net weight | 0.52 g | | |

Temperatures

Operating temperature -30 °C...90 °C

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|-----------------------------------|----------|-----------------------------------|--------------|
| Silicone | Yes | Number of wires | 1 |
| O.D. | 33.5 mm | Operating temperature range, max. | 90 °C |
| Operating temperature range, min. | -30 °C | Thickness | 3.00 mm |
| Cable gland | PG 21 | Basic material | Polyethylene |
| Diameter of sealing ring | 33.50 mm | Sealing | PE-HD |
| External thread | PG 21 | Internal thread | PG 21 |
| Inside diameter D2 | 28.30 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001181 | ETIM 9.0 | EC001181 |
| ETIM 10.0 | EC001181 | ECLASS 14.0 | 27-43-03-19 |
| ECLASS 15.0 | 27-43-03-19 | | |

Drawings

