

**GWDR PG29-PO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 29, Polyethylene
Order No.	<a href="#">1719500000</a>
Type	GWDR PG29-PO
GTIN (EAN)	4008190352769
Qty.	50 items

## GWDR PG29-PO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Height	3 mm	Height (inches)	0.1181 inch
Net weight	0.86 g		

### Temperatures

Operating temperature	-30 °C...90 °C
-----------------------	----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General information

Silicone	Yes	Number of wires	1
O.D.	43.5 mm	Operating temperature range, max.	90 °C
Operating temperature range, min.	-30 °C	Thickness	3.00 mm
Cable gland	PG, PG 29	Basic material	Polyethylene
Diameter of sealing ring	43.50 mm	Sealing	PE-HD
External thread	PG 29	Internal thread	PG 29
Inside diameter D2	37.00 mm		

### Classifications

ETIM 8.0	EC001181	ETIM 9.0	EC001181
ETIM 10.0	EC001181	ECLASS 14.0	27-43-03-19
ECLASS 15.0	27-43-03-19		

**Drawings**

