

GWDR PG48-PO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 48, Polyethylene
Order No.	1719530000
Type	GWDR PG48-PO
GTIN (EAN)	4008190352790
Qty.	5 items

GWDR PG48-PO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	3 mm	Height (inches)	0.1181 inch
Net weight	3.4 g		

Temperatures

Operating temperature -30 °C...90 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

Silicone	Yes	Number of wires	1
O.D.	69 mm	Operating temperature range, max.	90 °C
Operating temperature range, min.	-30 °C	Thickness	3.00 mm
Cable gland	PG 48	Basic material	Polyethylene
Diameter of sealing ring	69.00 mm	Sealing	PE-HD
External thread	PG 48	Internal thread	PG 48
Inside diameter D2	59.30 mm		

Classifications

ETIM 8.0	EC001181	ETIM 9.0	EC001181
ETIM 10.0	EC001181	ECLASS 14.0	27-43-03-19
ECLASS 15.0	27-43-03-19		

Drawings

