

GWDR PG9-NP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR NP (flat gasket - neoprene), Sealing ring, PG 9, Neoprene
Order No.	1719550000
Type	GWDR PG9-NP
GTIN (EAN)	4008190352813
Qty.	100 items

GWDR PG9-NP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	1.2 mm	Height (inches)	0.0472 inch
Net weight	0.36 g		

Temperatures

Operating temperature -40 °C... 100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

Silicone	No	Number of wires	1
O.D.	21 mm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Halogen	Yes
Thickness	1.20 mm	Cable gland	PG 9
Basic material	Neoprene	Diameter of sealing ring	21.00 mm
Sealing	Neoprene	External thread	PG 9
Internal thread	PG 9	Inside diameter D2	14.00 mm

Classifications

ETIM 8.0	EC001181	ETIM 9.0	EC001181
ETIM 10.0	EC001181	ECLASS 14.0	27-43-03-19
ECLASS 15.0	27-43-03-19		

Drawings

