

**GWDR PG11-NP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	GWDR NP (flat gasket - neoprene), Sealing ring, PG 11, Neoprene
Order No.	<a href="#">1719560000</a>
Type	GWDR PG11-NP
GTIN (EAN)	4008190352820
Qty.	100 items

**GWDR PG11-NP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Height	1.2 mm	Height (inches)	0.0472 inch
Net weight	0.42 g		

**Temperatures**

Operating temperature -40 °C... 100 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General information**

Silicone	No	Number of wires	1
O.D.	24 mm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Halogen	Yes
Thickness	1.20 mm	Cable gland	PG 11
Basic material	Neoprene	Diameter of sealing ring	24.00 mm
Sealing	Neoprene	External thread	PG 11
Internal thread	PG 11	Inside diameter D2	17.00 mm

**Classifications**

ETIM 8.0	EC001181	ETIM 9.0	EC001181
ETIM 10.0	EC001181	ECLASS 14.0	27-43-03-19
ECLASS 15.0	27-43-03-19		

**GWDR PG11-NP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

