

GWDR PG13,5-NP**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR NP (flat gasket - neoprene), Sealing ring, PG 13.5, Neoprene
Order No.	1719570000
Type	GWDR PG13,5-NP
GTIN (EAN)	4008 190352837
Qty.	100 items

GWDR PG13,5-NP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	1.2 mm	Height (inches)	0.0472 inch
Net weight	0.54 g		

Temperatures

Operating temperature -40 °C... 100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

Silicone	No	Number of wires	1
O.D.	27 mm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Halogen	Yes
Thickness	1.20 mm	Cable gland	PG 13.5
Basic material	Neoprene	Diameter of sealing ring	27.00 mm
Sealing	Neoprene	External thread	PG 13.5
Internal thread	PG 13.5	Inside diameter D2	19.50 mm

Classifications

ETIM 8.0	EC001181	ETIM 9.0	EC001181
ETIM 10.0	EC001181	ECLASS 14.0	27-43-03-19
ECLASS 15.0	27-43-03-19		

GWDR PG13,5-NP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

