

**GWDR PG21-NP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	GWDR NP (flat gasket - neoprene), Sealing ring, PG 21, Neoprene
Order No.	<a href="#">1719590000</a>
Type	GWDR PG21-NP
GTIN (EAN)	4008190352851
Qty.	100 items

## GWDR PG21-NP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Height	1.5 mm	Height (inches)	0.0591 inch
Net weight	0.86 g		

## Temperatures

Operating temperature	-40 °C... 100 °C
-----------------------	------------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General information

Silicone	No	Number of wires	1
O.D.	35 mm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Halogen	Yes
Thickness	1.50 mm	Cable gland	PG 21
Basic material	Neoprene	Diameter of sealing ring	35.00 mm
Sealing	Neoprene	External thread	PG 21
Internal thread	PG 21	Inside diameter D2	28.30 mm

## Classifications

ETIM 8.0	EC001181	ETIM 9.0	EC001181
ETIM 10.0	EC001181	ECLASS 14.0	27-43-03-19
ECLASS 15.0	27-43-03-19		

**GWDR PG21-NP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

